## JD200-SRR

Remote Seal – Threaded Type





## **Main Features**

Remote Seal Flange : Stainless Steel

Remote Seal Diaphragm : Stainless Steel, Hastelloy, Monel, Tantalum


Remote Seal Filling Oil : DC704, DC200, Neobee

Vaccum Process : Special Mouting For High Performance



## JD200-SRR

ORDER CODE





| PRODUCT   |                               |                           |                 |                    |                  |            |           |    |             |  |
|-----------|-------------------------------|---------------------------|-----------------|--------------------|------------------|------------|-----------|----|-------------|--|
| JD200-SRR | : Remote Seal - Threaded Type |                           |                 |                    |                  |            |           |    |             |  |
| •         | PROC                          | CESS CONNECTION           |                 |                    |                  |            |           |    |             |  |
|           | 1                             | : 1/4 NPT                 |                 |                    |                  |            |           |    |             |  |
| •         | 2                             | : 3/8 NPT                 |                 |                    |                  |            |           |    |             |  |
| •         | 3                             | : 1/2 NPT                 |                 |                    |                  |            |           |    |             |  |
|           | 4                             | : 3/4 NPT                 |                 |                    |                  |            |           |    |             |  |
|           | 5                             | :1 NPT                    |                 |                    |                  |            |           |    |             |  |
|           | 6                             | : 1 1/2 NPT               |                 |                    |                  |            |           |    |             |  |
|           |                               | FLANGE MATERIAL           |                 |                    |                  |            |           |    |             |  |
|           |                               | 1 : Stainless Steel       |                 |                    |                  |            |           |    |             |  |
|           |                               | FLANGE DIAPHRAGM MATERIAL |                 |                    |                  |            |           |    |             |  |
|           |                               |                           | 1               | : Stainless Steel  |                  |            |           |    |             |  |
|           |                               |                           | . 2 : Hastelloy |                    |                  |            |           |    |             |  |
|           |                               |                           | 3               | : Monel 400        |                  |            |           |    |             |  |
|           |                               |                           | 4               | : Tantlum          |                  |            |           |    |             |  |
|           |                               |                           | -               | FLANGE FILLING OIL |                  |            |           |    |             |  |
| •         |                               |                           | -               | 1 : Silicone DC704 |                  |            |           |    |             |  |
| •         |                               |                           | -               | 2 : Silicone DC200 |                  |            |           |    |             |  |
| •         |                               |                           | -               | 3 : Neobee         |                  |            |           |    |             |  |
| •         |                               |                           | -               | Z                  |                  |            |           |    |             |  |
|           |                               |                           |                 |                    | CAPILLARY LENGHT |            |           |    |             |  |
|           |                               |                           |                 |                    | 1                | : 1 meter  |           | 8  | : 8 meters  |  |
|           |                               |                           |                 |                    | 2                | : 2 meters |           | 9  | : 9 meters  |  |
|           |                               |                           | -               |                    | 3                | : 3 meters |           | Α  | : 10 meters |  |
|           |                               |                           |                 |                    | 4                | : 4 meters |           | В  | : 11 meters |  |
|           |                               |                           | -               |                    | 5                | : 5 meters |           | С  | : 12 meters |  |
|           |                               |                           | -               |                    | 6                | : 6 meters |           | Z  | : Special   |  |
|           |                               |                           | -               |                    | 7                | :7 me      |           |    |             |  |
|           |                               |                           |                 |                    |                  |            | UM PROCES | SS |             |  |
|           |                               |                           |                 |                    |                  | 0          | : No      |    |             |  |
|           |                               |                           |                 |                    |                  | 1          | : Yes     |    |             |  |
|           |                               |                           |                 |                    |                  |            | 1         |    |             |  |
| JD200-SRR | 1                             | 1                         | 1               | 1                  | 2                | 0          |           |    |             |  |

